

Aactive™ P printing dyes Cyanuric chloride																
Aactive™ P	C.I.№	Printing Depth		Solubility	Light ISO 150 BO2		Washing ISO 105 CO3		Perspiration Fastness ISO 105 EO4				Rubbing Fastness ISO 105x12		Chlorinated ISO 105-E03 ISO 105-X 12	
		5 GPL	30 GPL		g/l	1/3 SD	1/1 SD	CH	CO	Acid		Alkali		CH	CO	20 ppm
										CH	CO	CH	CO			
Yellow P-4G	Reactive Yellow 18			100	5	6	4-5	5	4-5	4	4-5	4	4-5	4	4	
Yellow P-8G	Reactive Yellow 85			150	5	6-7	4-5	5	4	4-5	5	4-5	4-5	4	3	
Brill. Yellow P-6G	Reactive Yellow 95			150	5	6-7	4-5	5	4	4-5	5	4-5	4-5	4	3	
Golden Yellow P-3R	Reactive Orange 12			100	5	6	4-5	4-5	4	3	4	3	4-5	4	4	
Brill. Orange P-2R	Reactive Orange 13			100	3-4	4-5	4-5	4-5	4-5	4	4-5	4	4-5	3	4	
P-GN	Brill Orange P-GN			70	4	4-5	4	4	4-5	4	4-5	4	4-5	3	4	
Red P-B	Reactive Red 24			100	4	4-5	4	4-5	4-5	4	4-5	4-5	4-5	2-3	4	
Red P-8B	Reactive Red 31			80	4	4-5	4-5	4	4	4	4	4	4	2-3	4	
Red P-3B	Reactive Red 45			100	4	4-5	4	4	4-5	4	4-5	4	4	2-3	4	
Red P-6B	Reactive Red 218			100	4	4-5	4	4	4-5	4	5	4	4	2-3	4	
Red P-4B	Reactive Red 245			100	4	4-5	4	4	4-5	4	4-5	4	4	2-3	4	
Blue P-GR	Reactive Blue 5			100	4	4-5	4-5	4	4	4	4	4	4	2-3	4	
Blue P-5R	Reactive Blue 13			80	4	4	3	4	4	3	4	3	4	2-3	4	
Navy Blue P-2R	Reactive Black 39			90	4	4-5	4	4	4-5	4	4-5	4	4-5	3	4	
Blue P-3R	Reactive Blue 49			100	4	4-5	4	4	4-5	4	4-5	4	4	2-3	4	
Turquoise Blue PGR	Reactive Blue 72			120	5	6-7	3-4	4-5	4-5	4-5	4	4	4	2-3	4	
Purple P-3R	Reactive Violet 1			100	4	4-5	4	4	4-5	4	4	4	4	2-3	4	
Magenta PB	Reactive Violet 46			100	4	4-5	4	4	4-5	4	4-5	4	4	2-3	4	
Brown P5BR	Reactive Brown 9			80	4	4-5	4	4	4-5	4	4	4	4	2-3	4	
Brown P-GR	Reactive Brown 11			80	4	4-5	4	4	4-5	4	4	4	4	2-3	4	
Black P-N	Reactive Black 8			80	4	4-5	4	4	4-5	4	4	4	4	2-3	4	
Black P-GR	Reactive Black Mix			100	4	4-5	4	4	4-5	4	4-5	4	4	2-3	4	